











Enabling Devices Communicator Feature Comparison



Non-Voice Devices

DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Eye Talks #3700, 3701, 3702, 3706	 A clear plastic communication device with a keyboard and a viewing window. The window has 'YES' and 'NO' labels on either side.	N/A — 17" x 11½" x 1/16"	N/A	N/A	N/A	N/A	We have constructed an adjustable and very affordable communication device that opens up a whole new world of social communication skills. The observer views the eye gaze of the user and sees their selection. The Eye-Talk is a great alternative for children and adults who need to communicate. It is made with clear, shatter-resistant plastic. Weight: ½ lb each.
Go! Boards 6 or 8 Icons #3336 & #3338	 A young boy is shown interacting with a blue vertical board. The board has several icon holders, some of which contain pictures.	6 or 8 — 2" x 2"	6 or 8	N/A	N/A	N/A	The Go! Board system is designed for individuals who would benefit from a picture schedule. Pictures or symbols representing a desired activity or task can be framed in the icon holders. When the activity is completed, the icon holder is removed and placed into the pocket at the base of the Go! Board. The Go! Board system is a valuable asset for any classroom that uses scheduling techniques. Both comes with a set of 2" x 2" icon holders. Size: 23" x 5½" x 3". Size: 29" x 5½" x 3". Weight: 1¼ lbs.



Single Message Devices





DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
<p>Big Talk #4200R, Y, B, G & P also Big Talk (Set of 5) #4106</p> <p>Mounted Big Talk (Red) #4204</p>		<p>1</p> <hr/> <p>5 1/4"</p>	1	20	Direct or Switch	Input Switch & Device Output	<p>Single message output with a large (5 1/4") activation surface. Device also acts as a switch so you can activate another device of your choice. Comes in five colors. Size: 7" x 4 1/2". Requires 4 AA Batteries. Weight: 1 lb.</p> <p>Our popular Big Talk comes with a mount! Includes 19" Gooseneck and Super Clamp. Easily attaches to any wheelchair or table. Weight: 3 1/4 lbs.</p>
<p>Mini-Com #9151</p>		<p>1</p> <hr/> <p>4" x 3 3/8"</p>	1	20	Direct	N/A	<p>Use these communicators individually or join them for building communication skills. Easy to use picture clip allows you to change icons easily. Size: 5 1/2"L x 6"W x 3"H. Requires 4 AA Batteries. Weight: 1/2 lb each.</p>
<p>NEW! One Message Communicator #4595</p>		<p>1</p> <hr/> <p>2 1/2"</p>	1	10	Direct	N/A	<p>Simple and affordable! Looking for a simple and affordable communicator? This is it! Record and play one 10-second message with the push of a button. Great for greetings and introductions or simple wants and needs. Comes with a clear icon cover. Size: 4 1/2"D x 2"H. Requires 3 AAA Batteries. Weight: 1/2 lb.</p>
<p>Put-Em-Arounds #9012, (Black) #9012B, (Set of 5) #9020, (Black) #9020B, (Set of 10) #9021, (Black) #9021B</p>		<p>1</p> <hr/> <p>5 1/4" x 3 3/4"</p>	1	20	Direct	N/A	<p>These talking wall communicators give users the ability to initiate communication throughout their day. Record your message (20 seconds) and allow them to actively participate with their peers, family, and teachers. Put them in different areas of your classroom or house to express simple messages. For example: "I'm hungry, I want a cookie"; "I have to use the bathroom". Wall mounting hardware is included. Some classrooms place them on lapboards or tabletops. Size 6 1/2"W x 8"L. Requires 4 AA Batteries. Weight: 1 lb.</p>



DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Palm Com #3068, (Set of 3) #3068T		1 — 1¼"	1	10	Direct	N/A	A great communicator that can be used many different ways – in the palm of your hand, clipped to your belt, or attached to your refrigerator or wall. Use alone or in sets. Each Palm Com features: Excellent sound quality, Small enough to fit in your pocket, Belt clip, magnet, and key ring connector on back, On/off switch, Volume control, Easy to record and re-record Size: 2½"L x 4¾"W x 1¼"H. Requires 3 AAA Batteries. Weight: ¼ lb.
Small Talk #4201R, Y, B, G & P also Small Talk (Set of 5) #4108		1 — 2½"	1	20	Direct or Switch	Input Switch & Device Output	The user can play recorded messages with the slightest touch on the small (2½") activation surface. A special holder allows you to show an icon, word or photo. Device also acts as a switch so you can activate a device when the message is playing. The Small Talk can also be activated by an external switch. Size: 2½"L x 5½"W x 5½"D. Requires 4 AAA Batteries. Weight: ½ lb.
Saucer Dome Say It Play It#9158		N/A — 6" x 3¼"	1	20	Direct	Device Output	Pressing the dome will reward the user with vibration and your pre-recorded message. It is easy to record and re-record any songs or words by pressing a hidden switch. A cord is provided which simultaneously activates an external device. Size: 8"W x 4½"H. Requires 6 AA Batteries. Weight: 1¼ lb.
Talking Alert #1412		1 — 5¼"	1 or 12	20 or 288	Direct or Switch	Input Switch	Pressing the textured lens turns on a bright light and starts your message. While the message is playing, a circle of lights indicate that words are being played. The 12-level unit allows you to record and play twelve 24-second messages. A special switch on the side of the unit selects levels. Has external switch capability. Size: 7¾"W x 2½"H. Requires 4 AA Batteries. Weight: 1 lb.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Talking Icon (Set of 3) #9199T		1 3"	1	10	Direct or Switch	Input Switch & Device Output	These small communicators can be used alone or attached together on a tabletop or wheelchair tray to initiate language. Excellent sound quality, On/Off switch & volume control, 3 square inch icon holder with Velcro, Velcro for attaching to another Talking Icon. Size: 4¾"L x 3½"W x 2½"H. Requires 3 AAA Batteries. Weight: 1¼ lbs.
Wrist Talker #3037 & #3037-B		1 1"	1	10	Direct	N/A	The slightest push on the face of this wrist communicator will provide a recorded message. Great sound quality will enable the user to communicate any greeting. Has an adjustable strap and is available in blue or black. Size: 2¼" x 1½". Requires 4 LR44 Button Cells (Included). Weight: ¼ lb.



Two Message Devices


DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Clip Talk #5520		N/A N/A	1 or 2	20	Direct or Switch	Input Switch	Our portable Clip Talk communicator allows you to record and re-record one 20-second or two 10-second messages. It contains a spring reinforced clip that snaps onto a wheelchair, walker, bedrail, stroller or virtually any other tubular or rectangular object. Size: 6½" x 4" x 5¼". Requires 4 AA Batteries. Weight: ½ lb.
Talkable II #2400		2 2½"	2	20	Direct	2 Device Outputs	This compact message communicator allows for simple communication and come with built-in icon holders. Size: 7½"L x 4½"W x 3"H. Requires 4 AAA Batteries. Weight: ¾ lb.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Textured Talkable II #2405		2 —	2	20	Direct	2 Device Outputs	This textured communicator provides the user with a fantastic tactile experience when they initiate language. It is great for quick communication. The different colored switches provide the user with good visual cues for choice making. Size: 8¾"L x 2¼"H x 7"W. Requires 4 AAA Batteries. Weight: 1 lb.
Twin Talks #1405, #1406, 1405X		2 — 3" x 5"	2	20	Direct	#1406 has a device output	Twin Talk is the ideal trainer, teacher and communicator. Use it to request attention, communicate needs, make simple choices, sing a song, make sound effects, participate in games, and more. Available in two helpful models: Twin Talk (speaks only) and Twin Talk and Play (simultaneously "speaks" and activates a toy or device). Size: 13" x 6½" x 2". Requires 4 AA Batteries. Weight: 1½ lbs.
Two Compartments Communicator #1243		2 — 2½" x 4¼"	2	20	Direct	N/A	Our exclusive compartmentalized communicator is fun, easy to use, and perfect for teaching language skills (classification, sequence, function, opposites and comparatives). Place objects, pictures or words in each of the compartments. Activating the switch plate plays the message while turning on one light at a time. Size: 11" x 10½" x 3". Requires 4 AA Batteries. Weight: 1½ lbs.
Rocking Plates #1398 Rocking Say It Play It #1399		2 — 12" x 3¼"	2	20	Direct	N/A — 2 Device Output	The Rocking Plate allows you to play two 10-second messages. For example, you could record yes/no responses to questions or any other desired messages. Size: 14"L x 6"W x 2½"H. Requires 4 AA Batteries. Weight: 1¼ lbs. Great for developing correlation between language and function. Our Say It Play It simultaneously activating two toys or devices using the cords (included) and plays back two messages. Size: 14"L x 6"W x 2½"H. Requires 4 AA Batteries. Weight: 1¼ lbs.




DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Rocking Two Message Say It Play It #1410		2 2" x 2"	2	20	Direct	N/A 2 Device Output	When you activate one switch, a message is played and an external toy or device is activated. Records two messages (10 seconds per message). Device has two switch outputs to activate 2 devices. Two 2" x 2" frames are attached to the switch plate so you can insert your own pictures or messages. Now with space to place your objects. Size: 5"L x 6"W x 1½"H. Requires 4 AA Batteries.
Wearable Talker #5022		2	2	20	Direct	N/A	Two messages! Our Wearable Talker is so versatile; you can wear it on any part of your body – your wrist, forearm, or leg – or place it on a wheelchair arm. Two clear covers for switches, Extra add-on strap. Size: 5½"L x 2¼"W x 1½"H. Requires 3 AAA Batteries. Weight: ¼ lb.






Three Message Devices






DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Grooved Platform Communicator #1910		3 4" x 4¼"	3	15	Direct	N/A	This colorful, creative tool is ideal for teaching communication skills and object/word relationships. Place objects, words or pictures on the raised platform, press the appropriate switch plate and lights and a 5-second pre-recorded voice message will play. Size: 16½" x 12" x 3½". Requires 4 AA Batteries. Weight: 2½ lbs.
Talkable III #2401		3 2½"	3	15	Direct	3 Device Outputs	This compact message communicator allows for simple communication and comes with built-in icon holders. Size: 7½"L x 4½"W x 3"H. Requires 4 AAA Batteries. Weight: 1 lb.




DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Three Compartment Communicator #1253		3 2½" x 4¼"	3	20	Direct	N/A	Our exclusive compartmentalized communicator is fun, easy to use, and perfect for teaching language skills (classification, sequence, function, opposites and comparatives). Place objects, pictures or words in each of the compartments. Comes with space for your objects and holders for your photos. Activating the switch plate plays the message while turning on one light at a time. Size: 14" x 10½" x 3". Requires 4 AA Batteries. Weight: 2½ lbs.


Four Message Devices




DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Cheap Talk 4 In-line #3054		4 2" x 2"	4	20	Direct	N/A	Activated by pressing one of the four squares. Size: 12½" x 3" x 6". Requires 4 AA Batteries. Weight: 1 lb.
Cheap Talk 4 Square #1392		4 2" x 2"	4	20	Direct	N/A	Activated by pressing one of four squares. Size: 8" x 8" x 3". Requires 4 AA Batteries. Weight: 1 lb.
Choice 4 Communicator #1237		4 2" x 2"	4 on 12 levels	300	Direct & Switch with Scanning	Input Switch	This unique communicator allows you to sequentially illuminate objects, photographs or icons with its super bright lights. The device also allows you to adjust the number of choices based upon the skills of the user. Work with just one field or add two, three or four fields. Size: 8"L x 15½"W x 3"H. Requires 4 D Batteries. Weight: 2¼ lbs.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Compact Communicators #1902		4 2" x 3"	3 4	15 20 sec	Direct	N/A	Go-anywhere communicator that can be used with pictures or objects. Small enough to fit comfortably on a lap or wheelchair table. The top of this mini communicator is compartmentalized allowing you to place the objects that are described in your pre-recorded messages. Pictures can also be placed in a special holder. Light goes on when switch plate is pressed and the message plays. Size: 11½"L x 6¼"W x 1½"H. Requires 4 AA Batteries. Weight: 1¼ lbs.
4-Plate Communicator Say It Play It #4055		4 3" x 5"	4	20	Direct	4 Device Outputs	This communicator provides a large target area for individuals who cannot easily access smaller communication devices. This versatile communicator can be positioned at a 30 degree angle or a 70 degree angle. The communicator also allows the user to simultaneously communicate and activate four different toys or devices. Size: 15"L x 7½"W x 7½"H. Requires 4 AA Batteries. Weight: 2 lbs.
Four Compartment #1245 & #1246		4 2½" x 4¼"	#1245 4 #1246 4 on 12 levels	20 288	#1245 Direct #1246 Direct & Switch w/2 scan modes	Input Switch	Pushing the colored plate below the icon holder plays your pre-recorded message while the bright light shines. #1246 has Linear scanning. Choose either automatic or inverse scanning with your external switch. Size: 18"L x 10"W x 6"H. Requires 4 AA Batteries. Weight: 2½ lbs.
Hip Talk 4 Message #5004		4 1" x 2"	4	20	Direct	N/A	Perfect for kids and adults alike, our unique Hip Talk communicators play messages at the push of a button. Come in a soft, nylon zippered pack with a waist strap. Size: 6¼" x 2¼" x 3¼". Requires 4 AA Batteries. Weight: ½ lb.
NEW! See & Speak Object Communicator #9259		4	12 levels	300	Direct	Device Output	Contain it! Do your instructional teaching materials get knocked to the ground? Our large clear container solves that problem. A simple communicator with a large plate to activate your messages about chosen objects. This classroom device provides great auditory and visual cues for your teaching time. This Communicator allows you to record four messages on 12 levels with a total recording time of 300 seconds or 6 seconds per message. It also acts as a switch to activate another device further enhancing your lesson. Velcro included for attaching two or more devices. Size: 10"L x 6½"W x 7½"H. Requires 4 AA Batteries. Weight: 1½ lbs.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Super-Sized Communicator #1221		4 2 3/4" x 4 1/4"	4 on 12 levels	288	Direct or Switch w/2 scan modes	Input Switch	Each compartment has its own switch for direct selection. Linear scanning allows the user to scan objects, photographs or symbols by activating a capability switch. Now choose either automatic or inverse scanning. Adjustable scan rate, easy to use photograph holder and easy to change icons. Size: 28"L x 11 1/2"W x 4 1/4"H. Requires 4 AA Batteries. Weight: 3 lbs.
Super Wrist Talker #5018		N/A	4 on 12 levels	20 to 240	Direct	N/A	Our compact Super Wrist Talker enables the user to communicate any need or greeting with its color coded button system. Has adjustable straps and is comfortable to wear. Size: 4"L x 2 1/4"W x 1"H. Requires 2 AAA Batteries. Weight: 1/4 lb.
Tabletop Compartment Communicator #1249		4 2" x 3"	4	20 sec on 12 levels	Direct or Switch w/2 scan modes	Input Switch	This tabletop communicator has it all - 12 levels, 2 scan modes, textured plates, and space for objects, photos and icons. Each compartment has its own switch for direct selection. Size: 12 1/2"L x 6"W x 3 1/2"H. Requires 4 AA Batteries. Weight: 1 1/2 lbs.
Take or Place N' Talk Series #8705 Upright Take N Talk #8709		4 Varies	1 to 4	20	Direct	Input Switch	Learning through actions...that is what our Take N' Talk Series devices strive to achieve. There are many different models available to suit your needs. Each is a self-contained device which allows the user to record 1 to 4 different 5 second messages. You play the messages back by removing "taking" an item (of your choice) (TAKE mode) or "placing" the item in one of the compartments (PLACE mode). Objects cannot be translucent/clear. Dish size: 7 1/2" x 1 1/2"; Box size: 6 3/4" x 4 1/4" x 2". Requires 4 AA Batteries.
Talk 4 w/Levels #2500 & #2500B		4 2 1/8" x 2 1/8"	4 on 12 levels	300	Direct & Switch w/Scanning	N/A	Our Talk 4 Augmentative Communicators are powerful communication tools loaded with useful features. Talk 4 has single switch illuminated auto scanning. It has a slot so you can easily slide in your icon overlay. Icon area requires only the slightest touch to play your "true voice" recording. The rugged and reliable Talk 4 is portable, lightweight and easy to access. Size: 11"L x 4"W x 2 3/4"H. Requires 4 AA Batteries. Weight: 1 lb.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Talkable IV #2402		4 2½"	4	20	Direct	4 Device Outputs	This compact message communicator allows for simple communication and comes with built-in icon holders. Size: 14"L x 5½"W x 2¾"H. Requires 4 AA Batteries. Weight: 1¼ lbs.
Sequencers							
DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Adjustable Angle Sequencer w/Switch #806		1 5"	Unlimited w/in 300 seconds	300	Direct	Device Output	Our sequencer is designed for the visually impaired. The circular patterned red LED lights in the center give the user a visual cue for targeting and encourage the user to activate the switch. The angle of the big 5" switch is adjustable from 32 degrees to 90 degrees. The light can be turned on or off. Size: 8"L x 8"W x 6¼"H. Requires 4 AA Batteries. Weight: 1¼ lbs.
Announcer w/6 Levels #5015		1 3"	10 Messages per level including level announcement 6 levels	5 sec per message total 300	Direct or Switch	Input Switch	Our sequencer communicator allows the user to first hear a series of words and then select one by simply activating its capability switch. Size: 26"H x 6"W. Requires 4 AA Batteries. Weight: 3 lbs.




DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Big Talk Triple Play #4202R, Y, B, G & P, (Set of 5) #4105		1 5¼"	Unlimited within total time 4 levels	75 sec per level total 300	Direct or Switch	Input Switch & Device Output	Single, sequential and random message capabilities with an output for activating other devices. Just push the round plate and your pre-recorded words can be played back in single, sequential or random order. Sequential capability is great for storytelling. Random capability is great for playing games that use dice, spinners, cards and more. Size: 7" x 4½". Requires 4 AA Batteries. Weight: 1 lb.
Mini-Com Sequencer #9151-S		1 4" x 3 3/8"	Unlimited w/in 300 seconds	300	Direct	N/A	We've added sequencing to our best-selling Mini-Com! Great for story telling, singing and joke telling. Size: 5½"L x 6"W x 3"H. Requires 4 AA Batteries. Weight: ½ lb.
Mounted Sequencer #5025		2 3"	1 to 250 messages	300	Direct of Switch	Input Switch	Play your messages in sequence by the slightest touch of the Red Gumball Switch. The 24" Gooseneck mount allows for easy access by the user. Record 1 to 250 messages with a total of 300 seconds of recording time. Great for conversation, storytelling, singing, joke telling, and game playing. Can also be used as a switch to activate a device. Size: 6"W x 29½"L including Gooseneck. Requires 4 AA Batteries. Weight: 3¼ lbs.
Small Talk Sequencer #8151, #8151Y, (Set of 3) #4107 Small Talk Sequencer w/Levels #8152, R, Y, (Set of 3) #8152T		1 2½"	250 75 seconds per level	300	Direct or Switch	Input Switch & Device Output	Single, sequential, and random message capabilities with an output for activating other devices. Sequential capability is great for storytelling, singing songs, telling a joke or carrying on a conversation with your friends. Press the plate the first time and the first message is spoken; press it again and the second message is spoken; etc. Random capability is great for playing games that use dice, spinners, cards and more. Size: 6¼"L x 6¼"W x 3"H. Requires 4 AAA Batteries. Weight: ¾ lb.

DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Speak a Need #1254		2 — 3"	10 Needs messages & 10 Response messages per level — 5 levels	300	Direct of Switch	Input Switch	A great auditory communicator for expressing your needs. Simple and fast to program and use. This versatile five level communicator allows the recording of five different categories of needs which could include food, bathing, and health needs. Once a category is chosen, pushing the red button sequences through a list of items (up to ten items) within that category. Size: 4"H x 8½"W x 4½"D. Requires 4 AAA Batteries. Weight: ¾ lb.
Step Talking Sequencers: #653 #673		Varies — Varies	Unlimited w/in 300 seconds	300	Direct	N/A	Our Step Talking Sequencers are perfect for the non-speaking adult or child. It allows the user to express a sequential series of your pre-recorded messages. The sequencer allows people with even the most limited communication skills to carry on a simple conversation. Ideal for a number of different purposes including sequencing, testing, directions, multiplication, memorization, medical instructions, storytelling and sing-alongs. #653 Size: 11" x 4½" x 2". Weight: 1½ lbs. #673 Size: 10" x 4½" x 2". Requires 4 AA Batteries. Weight: 1¼ lbs.
Talking Magic Roller #1652		N/A — N/A	Unlimited w/in 300 seconds	5 min	Direct & Switch	Input Switch for Base	The slightest touch rolls the cylinder and starts your story, songs or ABCs. This learning toy has a built-in sequential recorder which allows you to record and play. For example, roll and the first message is spoken; roll again and the second message is heard; etc. Simultaneously, the lights flash and the roller vibrates. Further, if the child cannot roll the unit, a capability switch (not included) can be used which runs on the built-in roller motor. The roller sequencer also can be removed from its stand and played with on a table or floor. Roller Size: 6"D x 6"H. Requires 4 AA Batteries. Base Size: 8½"L x 12"W x 5"H. Requires 2 AA Batteries. Weight: 3½ lbs.




Randomizers

DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Big Talk Triple Play #4202R, Y, B, G & P, (Set of 5) #4105		1 — 5¼"	Unlimited w/in 300 seconds — 4 levels	75 sec per level 300	Direct or Switch	Input Switch & Device Output	Single, sequential and random message capabilities with an output for activating other devices. Just push the round plate and your pre-recorded words can be played back in single, sequential or random order. Sequential capability is great for storytelling. Random capability is great for playing games that use dice, spinners, cards and more. One can play a message while activating your device. Size: 7" x 4½". Requires 4 AA Batteries. Weight: 1 lb.
Small Talk Sequencer #8151, #8151Y, (Set of 3) #4107 Small Talk Sequencer w/Levels #8152, R, Y, (Set of 3) #8152T		1 — 2½"	250 — 75 seconds per level	300	Direct or Switch	Input Switch & Device Output	Single, sequential, and random message capabilities with an output for activating other devices. Sequential capability is great for storytelling, singing songs, telling a joke or carrying on a conversation with your friends. Press the plate the first time and the first message is spoken; press it again and the second message is spoken; etc. Random capability is great for playing games that use dice, spinners, cards and more. Size: 6¼"L x 6¼"W x 3"H. Requires 4 AAA Batteries. Weight: ¾ lb.


Five to Seven Message Devices

DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Talkable 6 Spinning Communicator #2409		6 — 2½"	6	225	Direct	N/A	Our most popular communicators now come in a round, spinning version. A built-in Lazy Susan makes it easy to reach all six messages. Size: 8½"Diameter x 3"H. Requires 4 AAA Batteries. Weight: 1¼ lbs.
Placemat Communicator #8101, (Set) #8108X		6 — 4" x 4"	6	288	Direct	N/A	Our unique communicator is perfect for teaching language skills, requesting needs and making choices. Great for using at meal time to make food selections or to comment on the meal. The communicator is covered in soft clear protective plastic and has room for a plate or bowl and utensils. Simply raise the plastic and slide your size icons into the attached icon holders, record your message and you are ready to go. Size: 20"L x 4½"H x 19"W. Weight: 4 lbs.
7-Message Take or Place N' Talk Go! Board #3356		7 — 3" x 3"	7	245	Direct	N/A	Record seven messages then play the message back by removing or placing one of the 3" x 3" icon frames. Pocket on the front of the unit can be used for storage. Size: 29½" x 5¼" x 3". Requires 4 AA Batteries. Weight: ¾ lb.




Eight Message Devices

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Cheap Talk 8 #1391, 1391Bk		8 2" x 2"	8	300	Direct	N/A	Activated by pressing one of the eight message squares. Available in several models. Size: 12½" x 8" x 3". Requires 4 AA Batteries.
Cheap Talk 8 6-levels #2391, 2391Bk, 2391G, 2391M		8 2" x 2"	8 on 6 levels	288	Direct	N/A	Our exclusive 6-Level Communicator is ideal for teaching language skills and communicating. Messages can be recorded and re-recorded as often as you wish. Available in several models. Size: 12½"L x 8"W x 3"H. Requires 4 AA Batteries. Weight: 1½ lbs.
Talk 8 w/levels #2501B		8 2½" x 2½"	8 on 12 levels	600	Direct & Switches w/scanning	Input Switch	Our Talk 8 has direct access and two Switch scanning, Automatic scanning, Inverse scanning, and Step scanning. Requires only the slightest touch to play your "true voice" recording. The rugged and reliable Talk 8 is portable, lightweight and easy to access. Size: 11½"L x 6½"W x 3"H. Requires 4 AA Batteries. Weight: 1¼ lbs.





Nine to Fifteen Message Devices



DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Hip Talk 12 w/levels #5013		12 7/8"	60	300	Direct & Auditory Cueing	N/A	Our bestselling Hip Talk 12 has major improvements: 5 levels with easy level changer, 300 seconds of recording time, Incredible sound quality, Magnetic snap-on frame allows easy icon changing, New water resistant Neoprene carrying bag, Contoured for the waist, Adjustable waist strap to fit most, Sleep mode to save battery life, Volume control, Auditory cueing, On/Off switch. Size: 8½"L x 3"W x 3½"H. Requires 4 AA Batteries. Weight: 1 lb.

Sixteen to Sixty-Four Message Devices



DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Sentence Maker Communicator #2509		15 — 1 3/4" x 1 1/2"	15 on 7 levels	280	Direct & 3 additional access modes	N/A	Open up a world of communication choices with our new innovative Sentence Maker. The device allows the user to combine up to 15 of your pre-recorded words or short phrases to create their own unique sentences. The has FOUR modes: Direct Select with Auditory Queing, Single Switch Message Entry, Direct Select Beep Acknowledgement, and Direct Select. Size: 12 3/4"L x 10 3/4"W x 3 3/4"H. Requires 4 AA Batteries. Weight: 2 1/4 lbs.
Talking Photo Album #9127		24 — 4" x 6"	24 on 10 pages	240	Direct	N/A	Create a 24-page talking communication book with photographs, icons and drawings. Press the bottom of the page to start your message. (Requires a moderate amount of pressure.) Great to use as an interactive storyteller, choice maker or slide show. Size: 5 1/2"L x 7 3/4"W x 1 1/4"H. Requires 2 AAA Batteries. Weight: 1 1/4 lbs.
32-Message Communicator #3206		32 — 2" x 2"	32 on 6 levels	576	Direct	N/A	Frame allows for easy changing of overlays. Lightweight, portable and built to last, this communicator has adjustable legs for tilting the unit, is shock resistant and has its own carrying handle. Size: 16"L x 9"W x 3"H. Requires 4 AA Batteries. Weight: 2 1/2 lbs.






Progressive Communicators






DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Comm Builder #7071 & #7071B		1 to 16 — Varies (see website)	1 to 16	18 to 300	Direct	N/A	This Communication Builder is equipped with 5 easy to change frames, which allow you to refine communication choices as the person develops new skills. Record your own messages with the simplest push of a button. Light, durable and easy to carry with a built in handle. Frames included are 1, 2, 4, 8 and 16-window options. Re-recording is required when you change window frames. Frame size is 8½" x 7". Size: 12½"L x 9¼"W x 4"H. Requires 4 AA Batteries. Weight: 2¼ lbs.
4-Level Communication Builder #7077, #7077B (Black)		1 to 16 — Varies (see website)	1 to 16 on 7 levels	300	Direct	N/A	This Communication Builder is equipped with 5 easy to change frames, which allow you to refine communication choices as the person develops new skills. Additionally, a new feature allows this communicator to retain your recordings on all four levels when switching back and forth between window frames. Frame size is 8½" x 7". Size: 12½"L x 9¼"W x 4"H. Requires 4 AA Batteries. Weight: 2¼ lbs.
Hip Talk Plus #5020		3, 6, 12 — Varies (see website)	3, 6 or 12	300	Direct & Auditory Cueing	N/A	The ultimate and newly improved Hip Talk Plus has major changes: Incredible sound quality, Auditory cueing, Magnetic snap-on frames for easy icon changing, New waterproof Neoprene carrying bag, Contoured for the waist, Adjustable waist strap to fit most, Sleep mode to save battery life, Volume control, Low battery warning, 3 interchangeable frames. Size: 8½"L x 3"W x 3½"H. Requires 4 AA Batteries. Weight: 1 lb.
7-Level Communication Builder #7075 & #7075B On-the-Go 7-Level Communicator Builder #7075G		1 to 16 — Varies (see website)	1 to 16 on 7 levels	300	Direct	N/A	These Communication Builders allow the user to record and play back 1, 2, 4, 8, or 16 different messages per level. Re-recording is required when you change window frames. Time per level by window setting, using all seven levels. Frame size is 8½" x 7". Size: 12½"L x 9¼"W x 4"H. Requires 4 AA Batteries. Weight: 2¼ lbs.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Laptop Communicator - 7 Levels #7076		1 to 16 Varies	1 to 16 on 7 levels	300	Direct	N/A	This Communicator is a self-contained communication device, which allows the user to record and play back 1, 2, 4, 8 or 16 different messages per level. Re-recording is required when you change window frames. Frame size is 8½" x 7". Device size is 9½"L x 7½"W x 2¼"H. Requires 4 AA Batteries. Weight: 2¼ lbs.
Mountable 7-Level Communication Builder #7075M, #7075X		1 to 16 Varies (see website)	1 to 16 on 7 levels	300	Direct	N/A	These Communication Builders allow the user to record and play back 1, 2, 4, 8, or 16 different messages per level. Re-recording is required when you change window frames. Time per level by window setting, using all seven levels. Frame size is 8½" x 7". Size: 12½"L x 9¼"W x 4"H. Requires 4 AA Batteries. Weight: 2½ lbs to 4¾ lbs.




Devices for the Visually Impaired

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Adjustable Angle Sequencer w/Switch #806		1 5"	Unlimited within total time	300	Direct	Device Output	Our sequencer is designed for the visually impaired. The circular patterned red LED lights in the center give the user a visual cue for targeting and encourage the user to activate the switch. The angle of the big 5" switch is adjustable from 32 degrees to 90 degrees. Size: 8"L x 8"W x 6¼"H. Requires 4 AA Batteries. Weight: 1¼ lbs.
Cheap Talk 6 for VI #6056		6 2½"	6	225	Direct	N/A	The switches on our Cheap Talk 6 for VI are two different colors and outlined in black to make it easier to select your pre-recorded messages. Size: 20"L x 2½"H x 4¼"W. Requires 4 AA Batteries. Weight 2 lbs.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
4" x 5" Communicator for the VI #7083		8 — 4"	1 to 8 on 12 levels	300	Direct, Switch & Auditory Cueing	2 Input Switches	This state-of-the-art communicator for the visually impaired has large, brightly illuminated targets for activating your message choice. By pressing any of the icons or pictures it will illuminate your choice and play your pre-recorded message. Size: 19½"L x 17"W x 4"H. Requires 4 C and 4 AA Batteries. Weight: 7½ lbs.
Improved! Illuminated Picture Frame Communicator #1255		4 — 4" x 5"	4 on 12 levels	300	Direct, Switch & Auditory	Input Switch	Our brightly illuminated communicator was designed for those with visual impairments. Size: 12½"D x 19"W x 6"H. Requires 4 D Batteries. Weight: 4¼ lbs.
NEW! Light-up Put-em-Around #9049		1	1	20	Direct	N/A	We've added four bright LED lights to our popular Put-em-Around communicator. Any motion in front of the communicator will activate the lights. An adjustable sensitivity knob allows you to adjust the distance it takes to activate the lights (0 to 3 feet). Allows people with low vision to locate the communicator. See Put-em-Arounds (above) for detailed description of communicator features. Size: 8"L x 6½"W x 1½"H. Requires 4 AA Batteries. Weight: 1 lb.
Improved! Portable Communicator for the Visually Impaired #7081		8 — 3"	2 to 8 on 12 levels	600	Direct, Switch & Auditory Cueing	2 Input Switches	This unique state-of-the-art communicator provides intense background illumination of transparent icons. It is also extremely flexible – four scan modes and your choice of the number of fields to use. Size: 15"L x 9½"W x 2½"H. Requires 4 AA and 2 D Batteries. Weight: 2¾ lbs.
Portable 8 Message Communicator for the VI #7082		8 — 3" x 3"	6 levels	300 seconds	Direct	2 Input Switches	This cutting edge communicator has 8 large 3" x 3" icons which brightly light up when activating each message. The icons are also outlined in yellow for high contrast which makes it easier to locate the target area. In addition, small objects can be placed in each compartment which are also lit up when the message is activated. Size: 20"L x 13"W x 5½"H. Requires 4 C Batteries. Weight: 5 lbs.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Tactile Symbol Communicator #4040		6 4" x 4"	6 on 6 levels	216	Direct	N/A	Touch one of the six removable tactile symbols to activate a message and at the same time you will feel a vibration, which can be turned off if not desired. Tactile symbols are a graphic language system using concrete or abstract representations that are both permanent and manipulatable and can be tactually discriminated by an individual who is totally blind or dual sensory impaired. Size: 14"L x 10½"W x 2"H. Requires 4 AA Batteries. Weight: 3½ lbs.
Talking Alert #1412		1 5"	#1412 - 1 #1412-L - 12	20 288	Direct	N/A	Pressing the textured lens turns on a bright light and starts your message. While the message is playing, a circle of lights indicate that words are being played. A special switch on the side of the unit selects levels. Size: 7¾"W x 2½"H. Requires 4 AA Batteries. Weight: 1 lb.
Talkable II for VI #2600		2 2½"	2	20	Direct	2 Device Outputs	Our Talkable II for the VI is terrific for the visually impaired user. Two different colored switches are outlined in black to draw attention to the switch and make it easier to locate the target area. Size: 7½"L x 2¾"H x 4½"W. Requires 4 AAA Batteries. Weight: ¾ lb.
Totally Tactile Communicator #2046 (Black) & 2046Y (Yellow)		6 4½"	6 on 6 levels	300	Direct	N/A	Our tactile communicator is a wonderful place for the VI user to start communication. Our unique communicator has adjustable activation time (1-12 seconds) so you can feel the plates for a set time without activating the message. Size: 14½"L x 14½"W x 3"H. Requires 4 AA Batteries. Weight: 4 lbs.
NEW! Touch Screen Communicator #2408		1, 2 or 4	1 to 4	20	Direct	N/A	Simple easy messages! The slightest touch on the screen of this communicator will activate your message while the whole screen lights up. We've also added a motion sensor so any movement will light up the screen creating a cue for those with visual impairments. This Communicator comes with three frames for recording one, two or four messages and three blank mylar sheets for printing icons. Recording time for each message is 5 seconds. Comes with 3 frames - 1 Frame Size: 10 X 7½, 2 Frames Size: 7 x 3¾, 4 Frames Size: 4¾ x 3½. Size: 14½"L x 11½"W x 6"H. Requires 6 C Batteries. Weight: 5½ lbs.

Kits

DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Classroom Communication Kit #9037		See individual products in catalog or online!					<p>In consultation with special education teachers, assistive technology experts, and speech therapists, we put together a special Communication Kit for all your classroom needs. The communicators in this kit foster independence, enhance social interaction, and facilitate communication throughout your students' day. The Kit includes: Print It! Icon Maker #4069, Multi-Coms(2) #9155, Put 'Em Arounds Black (Set of 5) #9020B, Lighted Vibrating Mirror #358-M, Go! Board #3336, 7-Message Take or Place N' Talk Go Board #3347, Big Talk Triple Play #4202R, Talking Photo Album #9127, 7-Level Communication Builder #7075B, Cheap Talk 8, 6-Level #2392, Talkable III #2401, Twin Talk #1405. Weight: 22 lbs.</p>
Communicator Bundle #8100							<p>We've put together this great package - our bestselling 7-Level Communication Builder (#7075), Print-It Icon Maker (#4046), and a Communicator Case (#7752). Weight: 3 lbs.</p>
Quick Start Communication Kit #9024							<p>We've put together a basic kit of our best selling communicators for your classroom. These communicators will help your students with social interaction throughout their day. Small Talk Sequencer w/Levels (#8152), Big Talk Triple Play (Yellow) (#4202Y), Palm Com (#3068), Talkable III w/Built-in Icon Holders (#2401), Twin Talk (#1405), Put-em-Arounds (2) (#9012), Print It! Icon Maker (#4069). Weight: 8 lbs.</p>