







# Communicator Features Comparison Chart





## Non-Voice Devices

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Eye Talks #3700, 3701, 3702, 3712	 A white, adjustable communication device with a central opening and two side panels labeled 'YES' and 'NO'. It is supported by two black triangular feet.	N/A 17" x 11½" x 1/16"	N/A	N/A	N/A	N/A	We have constructed an adjustable and very affordable communication device that opens up a whole new world of social communication skills. The observer views the eye gaze of the user and sees their selection. The Eye-Talk is a great alternative for children and adults who need to communicate non-verbally. It is made with clear, shatter-resistant plastic. Weight: ½ lb each.
Go! Boards w/8 Icon Holders #3338	 A blue vertical board with eight yellow icon holders stacked vertically. Each holder contains a small icon.	8 2" x 2"	8	N/A	N/A	N/A	The Go! Board system is designed for individuals who would benefit from a picture schedule. Pictures or symbols representing a desired activity or task can be framed in the icon holders. When the activity is completed, the icon holder is removed and placed into the pocket at the base of the Go! Board. The Go! Board system is a valuable asset for any classroom that uses scheduling techniques. Comes with a set of 2" x 2" icon holders. Size: 22"L x 3"W x 2¾"H. Weight: 1¼ lbs.


## Single Message Devices

DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
<b>Big Talk</b> #4200R, Y, B, G & P also <b>Big Talk (Set of 5)</b> #4106		1 — 5¼"	1	20	Direct or Switch	Input Switch & Device Output	Single message output with a large (5¼") activation surface. Device also acts as a switch so you can activate another device of your choice. Comes in five colors. Size: 7" x 4½". Requires 4 AA Batteries. Weight: 1 lb.
<b>Mini-Com</b> #9151		1 — 4"	1	20	Direct	N/A	Use these communicators individually or join them for building communication skills. Easy to use picture clip allows you to change icons easily. Size: 5½"L x 6"W x 3"H. Requires 4 AA Batteries. Weight: ½ lb each.
<b>One Message Communicator</b> #4595		1 — 2½"	1	10	Direct	N/A	Simple and affordable! Looking for a simple and affordable communicator? This is it! Record and play one 10-second message with the push of a button. Great for greetings and introductions or simple wants and needs. Comes with a clear icon cover. Size: 4½"D x 2"H. Requires 3 AAA Batteries. Weight: ½ lb.
<b>Put-Em-Arounds</b> #9012, (Set of 5) #9020, (Set of 10) #9021		1 — 5¼" x 3¾"	1	20	Direct	N/A	These talking wall communicators give users the ability to initiate communication throughout their day. Record your message (20 seconds) and allow them to actively participate with their peers, family, and teachers. Put them in different areas of your classroom or house to express simple messages. For example: "I'm hungry, I want a cookie"; "I have to use the bathroom". Wall mounting hardware is included. Some classrooms place them on lapboards or tabletops. Size 6½"W x 8"L. Requires 4 AA Batteries. Weight: 1 lb.





## Two Message Devices

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Clip Talk #5520		N/A — N/A	1 or 2	20	Direct or Switch	Input Switch	Our portable Clip Talk communicator allows you to record and re-record one 20-second or two 10-second messages. It contains a spring reinforced clip that snaps onto a wheelchair, walker, bedrail, stroller or virtually any other tubular or rectangular object. Size: 6½" x 4" x 5¼". Requires 4 AA Batteries. Weight: ½ lb.
Talkable 2 #2400		2 — 2½"	2	20	Direct	2 Device Outputs	This compact message communicator allows for simple communication and comes with built-in icon holders. Size: 7½"L x 4½"W x 3"H. Requires 4 AAA Batteries. Weight: ¾ lb.
Twin Talks #1405, 1405X		2 — 3" x 5"	2	20	Direct	N/A	Twin Talk is the ideal trainer, teacher and communicator. Use it to request attention, communicate needs, make simple choices, sing a song, make sound effects, participate in games, and more. Size: 13" x 6½" x 2". Requires 4 AA Batteries. Weight: 1½ lbs.
Rocking Say It Play It #1399		2 — 12" x 3¼"	2	20	Direct	2 Device Output	Great for developing correlation between language and function. Our Say It Play It simultaneously activating two toys or devices using the cords (included) and plays back two messages. Size: 14"L x 6"W x 2½"H. Requires 4 AA Batteries. Weight: 1¼ lbs.


## Three Message Devices

DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Talkable 3 #2401		3 — 2½"	3	15	Direct	3 Device Outputs	This compact message communicator allows for simple communication and comes with built-in icon holders. Size: 7½"L x 4½"W x 3"H. Requires 4 AAA Batteries. Weight: 1 lb.


## Four Message Devices

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
<b>4-Plate Communicator Say It Play It #4055</b>		4 — 3" x 5"	4	20	Direct	4 Device Outputs	This communicator provides a large target area for individuals who cannot easily access smaller communication devices. This versatile communicator can be positioned at a 30 degree angle or a 70 degree angle. The communicator also allows the user to simultaneously communicate and activate four different toys or devices. Size: 15"L x 7½"W x 7½"H. Requires 4 AA Batteries. Weight: 2 lbs.
<b>Tactile Communicator Say It Play It #4210</b>		4 — 2" x 2"	4	20	Direct	4 Device Outputs	The Tactile Say It Play It packs a lot into one device, acting as both communicator and switch. Press any of the four plates to play a pre-recorded message and simultaneously activate a toy or device. The four different raised patterns on the plates and the yellow-on-black color scheme make it perfect for the visually impaired. Easily record messages of up to 5 seconds each. Four cords that pair with any switch-adapted device are included. Size: 10½"L x 4½"W x 2"H. Requires 4 AA. Batteries. Weight: 1½ lbs.
<b>Basic Talk 4 #4047B &amp; Talk 4 w/Levels #2500B</b>		4 — 2½" x 2½"	4 (Basic) — 4 on 12 levels	20 — 480	Direct & Switch w/Scanning	N/A	Our Talk 4 Augmentative Communicators are powerful communication tools loaded with useful features. Talk 4 has single switch illuminated auto scanning. It has a slot so you can easily slide in your icon overlay. Icon area requires only the slightest touch to play your "true voice" recording. The rugged and reliable Talk 4 is portable, lightweight and easy to access. Size: 11"L x 4"W x 2¾"H. Requires 4 AA Batteries. Weight: 1 lb.
<b>Talkable 4 #2402 &amp; Talkable 4 w/12 Levels #2403</b>		4 — 2½"	4 — 4 on 12 levels	20 — 480	Direct	4 Device Outputs	This compact message communicator allows for simple communication and comes with built-in icon holders. Size: 14"L x 5½"W x 2¾"H. Requires 4 AA Batteries. Weight: 1¼ lbs.



# Sequencers

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
<b>Adjustable Angle Sequencer w/Switch #806</b>		1 — 5"	Unlimited w/in 300 seconds	480	Direct	Device Output	Our sequencer is designed for the visually impaired. The circular patterned red LED lights in the center give the user a visual cue for targeting and encourage the user to activate the switch. The angle of the big 5" switch is adjustable from 32 degrees to 90 degrees. The light can be turned on or off. Size: 8"L x 8"W x 6¼"H. Requires 4 AA Batteries. Weight: 1¼ lbs.
<b>Big Talk Triple Play #4202R, Y, B, G &amp; P, (Set of 5) #4105</b>		1 — 5¼"	Unlimited within total time — 4 levels	120 sec per level — total 480	Direct or Switch	Input Switch & Device Output	Single, sequential and random message capabilities with an output for activating other devices. Just push the round plate and your pre-recorded words can be played back in single, sequential or random order. Sequential capability is great for storytelling. Random capability is great for playing games that use dice, spinners, cards and more. Size: 7" x 4½". Requires 4 AA Batteries. Weight: 1 lb.
<b>Small Talk Sequencer #8151, (Set of 3) #4107</b>		1 — 2½"	250	480	Direct or Switch	Input Switch & Device Output	Single, sequential, and random message capabilities with an output for activating other devices. Sequential capability is great for storytelling, singing songs, telling a joke or carrying on a conversation with your friends. Press the plate the first time and the first message is spoken; press it again and the second message is spoken; etc. Random capability is great for playing games that use dice, spinners, cards and more. Size: 6¼"L x 6¼"W x 3"H. Requires 4 AAA Batteries. Weight: ¾ lb.



## Randomizers

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
<b>Big Talk Triple Play</b> #4202R, Y, B, G & P, (Set of 5) #4105		1 <hr style="width: 20px; margin: 0 auto;"/> 5¼"	Unlimited w/in 300 seconds <hr style="width: 20px; margin: 0 auto;"/> 4 levels	120 sec per level <hr style="width: 20px; margin: 0 auto;"/> total 480	Direct or Switch	Input Switch & Device Output	Single, sequential and random message capabilities with an output for activating other devices. Just push the round plate and your pre-recorded words can be played back in single, sequential or random order. Sequential capability is great for storytelling. Random capability is great for playing games that use dice, spinners, cards and more. One can play a message while activating your device. Size: 7" x 4½". Requires 4 AA Batteries. Weight: 1 lb.
<b>Small Talk Sequencer</b> #8151, (Set of 3) #4107		1 <hr style="width: 20px; margin: 0 auto;"/> 2½"	250	480	Direct or Switch	Input Switch & Device Output	Single, sequential, and random message capabilities with an output for activating other devices. Sequential capability is great for storytelling, singing songs, telling a joke or carrying on a conversation with your friends. Press the plate the first time and the first message is spoken; press it again and the second message is spoken; etc. Random capability is great for playing games that use dice, spinners, cards and more. Size: 6¼"L x 6¼"W x 3"H. Requires 4 AAA Batteries. Weight: ¾ lb.



## Five to Seven Message Devices

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
<b>Talkable 6 Spinning Communicator #2409</b>		6 <hr/> 2½"	6	480	Direct	N/A	<p>Our most popular communicators now come in a round, spinning version. A built-in Lazy Susan makes it easy to reach all six messages.</p> <p>Size: 8½"Diameter x 3"H. Requires 4 AAA Batteries. Weight: 1¼ lbs.</p>
<b>7-Message Take or Place N' Talk Go! Board #3356</b>		7 <hr/> 3" x 3"	7	480	Direct	N/A	<p>Record seven messages then play the message back by removing or placing one of the 3" x 3" icon frames. Pocket on the front of the unit can be used for storage. Size: 24½" x 4¼" x 2¼". Requires 4 AA Batteries. Weight: 3 lb.</p>




## Eight Message Devices

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Cheap Talk 8 #1391		<p style="text-align: center;">8 — 2" x 2"</p>	<p style="text-align: center;">8</p>	<p style="text-align: center;">480</p>	<p style="text-align: center;">Direct</p>	<p style="text-align: center;">N/A</p>	<p>Activated by pressing one of the eight message squares. Size: 10½"L x 6¼"W x 3"H. Requires 4 AA Batteries. Weight: 2 lbs.</p>
Cheap Talk 8 6-levels #2391		<p style="text-align: center;">8 — 2" x 2"</p>	<p style="text-align: center;">8 on 6 levels</p>	<p style="text-align: center;">480</p>	<p style="text-align: center;">Direct</p>	<p style="text-align: center;">N/A</p>	<p>Our exclusive 6-Level Communicator is ideal for teaching language skills and communicating. Messages can be recorded and re-recorded as often as you wish. Size: 10½"L x 6¼"W x 3"H. Requires 4 AA Batteries. Weight: 2 lbs.</p>





## Sixteen to Sixty-Four Message Devices

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Talking Photo Album #9127		<p style="text-align: center;">24</p> <hr style="width: 20%; margin: auto;"/> <p style="text-align: center;">4" x 6"</p>	24 on 10 pages	240	Direct	N/A	<p>Create a 24-page talking communication book with photographs, icons and drawings. Press the bottom of the page to start your message. (Requires a moderate amount of pressure.) Great to use as an interactive storyteller, choice maker or slide show. Size: 5½"L x 7¾"W x 1¼"H. Requires 2 AAA Batteries. Weight: 1¼ lbs.</p>
32-Message Communicator #3206		<p style="text-align: center;">32</p> <hr style="width: 20%; margin: auto;"/> <p style="text-align: center;">2" x 2"</p>	32 on 6 levels	480	Direct	N/A	<p>Frame allows for easy changing of overlays. Lightweight, portable and built to last, this communicator has adjustable legs for tilting the unit, is shock resistant and has its own carrying handle. Size: 16"L x 9"W x 3"H. Requires 4 AA Batteries. Weight: 2½ lbs.</p>

## Progressive Communicators

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
Communication Builder #7071		1 to 16 — Varies (see website)	1 to 16	18 to 300	Direct	N/A	This Communication Builder is equipped with 5 easy to change frames, which allow you to refine communication choices as the person develops new skills. Record your own messages with the simplest push of a button. Light, durable and easy to carry with a built in handle. Frames included are 1, 2, 4, 8 and 16-window options. Re-recording is required when you change window frames. Frame size is 8½" x 7". Size: 10¾"L x 8¼"W x 3"H. Requires 4 AA Batteries. Weight: 2¼ lbs.
Hip Talk Plus #5020		3, 6, 12 — Varies (see website)	3, 6 or 12	480	Direct & Auditory Cueing	N/A	The ultimate and newly improved Hip Talk Plus has major changes: incredible sound quality, auditory cueing, magnetic snap-on frames for easy icon changing, new waterproof Neoprene carrying bag, contoured for the waist, adjustable waist strap to fit most, sleep mode to save battery life, volume control, Low battery warning, 3 interchangeable frames. Size: 8½"L x 3"W x 3½"H. Requires 4 AA Batteries. Weight: 1 lb.
7-Level Communication Builder #7075		1 to 16 — Varies (see website)	1 to 16 on 7 levels	480	Direct	N/A	This communication builder allows the user to record and play back 1, 2, 4, 8, or 16 different messages per level. Re-recording is required when you change window frames. Time per level by window setting, using all seven levels. Choice of blue or black. Frame size is 8½" x 7". Size: 10¾"L x 8¼"W x 3"H. Requires 4 AA Batteries. Weight: 2¼ lbs.

## Devices for the Visually Impaired

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
<b>Adjustable Angle Sequencer w/Switch #806</b>		1 — 5"	Unlimited within total time	480	Direct	Device Output	Our sequencer is designed for the visually impaired. The circular patterned red LED lights in the center give the user a visual cue for targeting and encourage the user to activate the switch. The angle of the big 5" switch is adjustable from 32 degrees to 90 degrees. Size: 8"L x 8"W x 6¼"H. Requires 4 AA Batteries. Weight: 1¼ lbs.
<b>Cheap Talk 6 for VI #6056</b>		6 — 2½"	6	480	Direct	N/A	The switches on our Cheap Talk 6 for VI are two different colors and outlined in black to make it easier to select your pre-recorded messages. Size: 20"L x 2½"H x 4¾"W. Requires 4 AA Batteries. Weight 2 lbs.
<b>4" x 5" Communicator for the VI #7083</b>		8 — 4"	1 to 8 on 12 levels	480	Direct, Switch & Auditory Cueing	2 Input Switches	This state-of-the-art communicator for the visually impaired has large, brightly illuminated targets for activating your message choice. By pressing any of the icons or pictures it will illuminate your choice and play your pre-recorded message. Size: 18"L x 12"W x 4"H. Requires 4 C and 4 AA Batteries. Weight: 7½ lbs.
<b>In-Line 4 Communicator for the VI #7089</b>		4 — 4"	1 to 4 on 12 levels	480	Direct, Switch & Auditory Cueing	2 Input Switches	This brand new communicator is designed for the visually impaired but can be beneficial for anyone who needs a larger target area. This in-line communicator has 12 levels with 300 seconds of recording time; a jack for automatic scanning; and large, brightly illuminated targets that make it possible to see, select and activate messages. The target lights up when activated by direct select or switch scanning and the pre-recorded message plays. Four-by-five-inch icons slip easily under clear overlays. Size: 18"L x 6½"D x 3½"H. Requires 4 AA Batteries. Weight: 3½ lbs.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
<b>Tactile Symbol Communicator</b> #4040		6 — 4" x 4"	6 on 6 levels	480	Direct	N/A	Uniquely designed for those who are blind or dually sensory impaired, this six level communicator has room for 36 six-second messages. Create your own personal tactile symbols using everyday objects. Velcro included for attaching your tactile icons. Size: 14"L x 10½"W x 2"H. Requires 4 AA Batteries. Weight: 3½ lbs.
<b>Talkable 2 for VI</b> #2600		2 — 2½"	2	20	Direct	2 Device Outputs	Our Talkable II for the VI is terrific for the visually impaired user. Two different colored switches are outlined in black to draw attention to the switch and make it easier to locate the target area. Size: 7½"L x 2¾"H x 4½"W. Requires 4 AAA Batteries. Weight: ¾ lb.
<b>Totally Tactile Communicator</b> #2046 (Black)		6 — 4½"	6 on 6 levels	480	Direct	N/A	Our tactile communicator is a wonderful place for the VI user to start communication. Our unique communicator has adjustable activation time (1-12 seconds) so you can feel the plates for a set time without activating the message. Size: 14½"L x 14½"W x 3"H. Requires 4 AA Batteries. Weight: 4 lbs.

# Kits

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	FEATURES
<b>Classroom Communication Kit</b> #9037		<b>See individual products in catalog or online!</b>					<p>In consultation with special education teachers, assistive technology experts, and speech therapists, we put together a special Communication Kit for all your classroom needs. The communicators in this kit foster independence, enhance social interaction, and facilitate communication throughout your students' day. The Kit includes: Print It! Icon Maker #4069X, Mini-Com #9151, Put 'Em Arounds (Set of 5) #9020, Lighted Vibrating Mirror #358-M, Go! Board #3338, 7-Message Take or Place N' Talk Go Board #3356, Big Talk Triple Play #4202R, Talking Photo Album #9127, 7-Level Communication Builder #7075B, Cheap Talk 8, 6-Level #2391, Talkable III #2401, Twin Talk #1405. Weight: 22 lbs.</p>
<b>Quick Start Communication Kit</b> #9024		<b>See individual products in catalog or online!</b>					<p>We've put together a basic kit of our best selling communicators for your classroom. These communicators will help your students with social interaction throughout their day. Small Talk Sequencer w/Levels (#8152), Big Talk Triple Play (Yellow) (#4202Y), Mini-Com (#9151), Talkable III w/Built-in Icon Holders (#2401), Twin Talk (#1405), Put-em-Arounds (2) (#9012), Print It! Icon Maker (#4069X). Weight: 8 lbs.</p>